

# Eaton ENR32201 GFI

Catalog Number: ENR32201 GFI

Eaton Crouse-Hinds series Ark-Gard ENR-GFCI kit, 20A, 50-400 Hz, Copper-free aluminum, 5-20R, Two-gang, Dead end, 1", 125 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR-GFCI kit	ENR32201 GFI
	UPC
	662276253445
Product Length/Depth	Product Height
8 in	6.72 in
Product Width	Product Weight
7.56 in	0.999 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Amperage Rating

20A

### Voltage rating

125 Vac

### Style

Dead end

### Trade size

1"

### NEMA configuration

5-20R

### Number of gangs

Two-gang

### Material

Copper-free aluminum

### Frequency rating

50-400 Hz

## Resources

### Catalogs

[Ark-Gard Hazardous Area ENR-GFCI Kits catalog page](#)

### Specifications and datasheets

[Eaton Specification Sheet - ENR32201 GFI](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)