

Eaton ENR5151

Catalog Number: ENR5151

Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle, 15A, 50-400 Hz, Copper-free aluminum, 5-15R, 125 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle	ENR5151
	UPC
	782274183367
Product Length/Depth	Product Height
3.01 in	5.09 in
Product Width	Product Weight
4.86 in	1.9 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Amperage Rating

15A

Voltage rating

125 Vac

Style

Dead end

NEMA configuration

5-15R

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ENR5151 3D drawing](#)

Catalogs

[Ark-Gard ENR Value Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

Specifications and datasheets

[Eaton Specification Sheet - ENR5151](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)