

Eaton ENRC12201 GFI

Catalog Number: ENRC12201 GFI

Eaton Crouse-Hinds series Ark-Gard ENR-GFCI kit, 20A, 50-400 Hz, Copper-free aluminum, 5-20R, Two-gang, Through feed, 1/2", 125 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR-GFCI kit	ENRC12201 GFI
	UPC
	662276253452
Product Length/Depth	Product Height
8 in	6.72 in
Product Width	Product Weight
7.56 in	0.999 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Amperage Rating

20A

Voltage rating

125 Vac

Style

Through feed

Trade size

1/2"

NEMA configuration

5-20R

Number of gangs

Two-gang

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

Catalogs

[Ark-Gard Hazardous Area ENR-GFCI Kits catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - ENRC12201 GFI](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)