

# Eaton ENRC22151 M4

Catalog Number: ENRC22151 M4

Eaton Crouse-Hinds series Ark-Gard ENR Premier receptacle assembly, 15A, Double, 50-400 Hz, Copper-free aluminum, 5-15R, Two-gang, Through feed, 3/4", 125 Vac

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Ark-Gard ENR Premier receptacle assembly	ENRC22151 M4  UPC 662276174337
<b>Product Length/Depth</b>	<b>Product Height</b>
6.78 in	6.75 in
<b>Product Width</b>	<b>Product Weight</b>
7.56 in	1 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

3R

7

9

12

## Product specifications

### Number of gangs

Two-gang

### Amperage Rating

15A

### Voltage rating

125 Vac

### Style

Through feed

### Trade size

3/4"

### NEMA configuration

5-15R

### Cover type

Double

### Material

Copper-free aluminum

### Frequency rating

50-400 Hz

## Resources

### Catalogs

[Ark-Gard ENR Premier Explosionproof NEMA Locking Devices catalog page](#)

### Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

### Installation instructions

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

[IF 1588 - ENR M4 Series Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - ENRC22151 M4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)