

Eaton ENRC22201 M4

Catalog Number: ENRC22201 M4

Eaton Crouse-Hinds series Ark-Gard ENR Premier receptacle assembly, 20A, Double, 50-400 Hz, Copper-free aluminum, 5-20R, Two-gang, Through feed, 3/4", 125 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENR Premier receptacle assembly	ENRC22201 M4 UPC 662276174290
Product Length/Depth	Product Height
6.78 in	6.75 in
Product Width	Product Weight
7.56 in	1 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

3R

7

9

12

Product specifications

Number of gangs

Two-gang

Amperage Rating

20A

Voltage rating

125 Vac

Style

Through feed

Trade size

3/4"

NEMA configuration

5-20R

Cover type

Double

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

Catalogs

[Ark-Gard ENR Premier Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

Installation instructions

[IF 1588 - ENR M4 Series Receptacles](#)

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

Specifications and datasheets

[Eaton Specification Sheet - ENRC22201 M4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)