

Eaton EPC604 2042 WT225 3

Catalog Number: EPC604 2042 WT225 3

Eaton Crouse-Hinds series Arktite EPC interlocked receptacle, 200A, 225A circuit breaker, 3-wire, 4-pole, With breaker, 225A frame, Style 2, Cutler-Hammer, Copper-free alum, Spring door, 3", Interchangeable thermal trip, 600 Vac/250 Vdc

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite EPC interlocked receptacle	EPC604 2042 WT225 3
	UPC
	782274025360
Product Length/Depth	Product Height
18 in	36 in
Product Width	Product Weight
27 in	257 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Frame size

225A

Type

Interchangeable thermal trip

Enclosure type

With breaker

Amperage Rating

200A

Grounding style

Style 2

Configuration

Three-wire, four-pole

Voltage rating

600 Vac/250 Vdc

Trade size

3"

Circuit breaker amperage

225A

Manufacturer

Cutler-Hammer

Material

Copper-free aluminum

Receptacle style

Spring door

Resources

Catalogs

[Arktite EPC and EPCB Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[Arktite EPC/EPCB Explosionproof Interlock Receptacles with Circuit Breakers UL certification](#)

Installation instructions

[IF 1634 - EPC 200A Bail Assembly Replacement](#)

[IF 267 - EPC Interlocked Receptacle](#)

IF 1239 - EPC 200A Interlocked Receptacle

Specifications and datasheets

Eaton Specification Sheet - EPC604 2042 WT225 3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)