

# Eaton EV25-175

Catalog Number: EV25-175

Eaton Bussmann series high speed hybrid and electric vehicles fuse, Eaton Bussmann series EV Fuse, 25mm, 175, High Speed, Non Indicating

## General specifications



**BUSSMANN**  
SERIES

Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series high speed hybrid and electric vehicles fuse	EV25-175
	<b>UPC</b>
	051712518543
<b>Product Length/Depth</b>	<b>Product Height</b>
92.23 mm	25.4 mm
<b>Product Width</b>	<b>Product Weight</b>
25.4 mm	8 g
<b>Compliances</b>	<b>Certifications</b>
REACH	Contact Manufacturer
JASO D622	
RoHS Compliant	

## Type

Fuse

## Application

Hybrid and Electric vehicles

## Amperage Rating

175 A

## With striker

No

## Voltage type

DC

## Fuse indicator

Non Indicating

## Electrical characteristics

High Speed

## Watt losses

5.25 W

## Packaging type

Standard

## Voltage rating

500 V

## Catalogs

EV25-175~25MM EV FUSE

[Bussmann series complete full line catalog no. 1007](#)

## Specifications and datasheets

[Eaton Specification Sheet - EV25-175](#)