

# Eaton EXH5 480160 150

Catalog Number: EXH5 480160 150

Eaton Crouse-Hinds series EXH electric air heater, 60 Hz, 51,200 BTU/hr, 15 kW, Steel, 31.3A max., Single-phase, 27.1°F (15.1°C) temperature rise, 480 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series EXH electric air heater	EXH5 480160 150
	UPC
	662276362468
Product Length/Depth	Product Height
23.44 in	22.5 in
Product Width	Product Weight
22.63 in	168 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

### NEMA Rating

7

9

## Product specifications

### Voltage rating

480 Vac

### Phase

Single-phase

### Frequency rating

60 Hz

### Power output

15 kW

### Maximum total amperage

31.3 A

### Heat output

51,200 BTU/hr

### Temperature rise

27.1°F (15.1°C)

### Material

Steel

## Resources

### Catalogs

[EXH Series Explosionproof Electric Heater catalog page](#)

### Certification reports

[EXH Explosionproof Electric Heaters Canadian certification](#)

[EXH Explosionproof Electric Heaters UL certification](#)

### Installation instructions

[IF 11592 - EXH5 Series Explosionproof Electric Heater](#)

### Specifications and datasheets

[Eaton Specification Sheet - EXH5 480160 150](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)