

Eaton EXH5 480360 050

Catalog Number: EXH5 480360 050

Eaton Crouse-Hinds series EXH electric air heater, 60 Hz, 17,100 BTU/hr, 5 kW, Steel, 6.0A max., Three-phase, 18.6°F (10.3°C) temperature rise, 480 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series EXH electric air heater	EXH5 480360 050
	UPC 662276287808
Product Length/Depth	Product Height
19.47 in	18.5 in
Product Width	Product Weight
22.63 in	140 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

NEMA Rating

7

9

Product specifications

Voltage rating

480 Vac

Phase

Three-phase

Frequency rating

60 Hz

Power output

5 kW

Maximum total amperage

6 A

Heat output

17,100 BTU/hr

Temperature rise

18.6°F (10.3°C)

Material

Steel

Resources

Catalogs

[EXH Series Explosionproof Electric Heater catalog page](#)

Certification reports

[EXH Explosionproof Electric Heaters Canadian certification](#)

[EXH Explosionproof Electric Heaters UL certification](#)

Installation instructions

[IF 11592 - EXH5 Series Explosionproof Electric Heater](#)

Specifications and datasheets

[Eaton Specification Sheet - EXH5 480360 050](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)