

Eaton FAZ-C50{3-RT

Catalog Number: FAZ-C50/3-RT

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,50 A,10 kAIC, 14 kAIC,Three-pole,277/480 V,5-10X /n,50-60 Hz, Ring-tongue terminals,C Curve

General specifications



Photo is representative

Product Name

Eaton FAZ branch protector

Catalog Number

FAZ-C50/3-RT

EAN

4015081904549

Product Length/Depth

2.5 in

Product Height

4 in

Product Width

2.75 in

Product Weight

0.92 lb

Warranty

1 year

Certifications

UL 489



Powering Business Worldwide

Physical Attributes

Number of poles

Three-pole

Terminals

Ring-tongue

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

14 kAIC

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/3-RT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)