

Eaton FIG 1000 2X1 1/4 FASTC EG

Catalog Number: FIG 1000 2X1 1/4 FASTC EG

Eaton B-Line series TOLCO lateral sway brace attachment, Electro-galvanized, Steel, Fig 1000, 2" pipe size with 1.25" brace pipe, Fast clamp sway brace attachment

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series TOLCO lateral sway brace attachment	FIG 1000 2X1 1/4 FASTC EG
	UPC
	782051720921
Product Length/Depth	Product Height
0 in	1.25 in
Product Width	Product Diameter
0 in	1 in
Product Weight	Certifications
8.8 lb	OSHPD Certified
	UL Listed

Material type

Finish

Electro-plated

Material

Steel

Product dimension

Size

2 inch pipe size with 1.25 inch brace pipe

Other product information

Model

Fig 1000

Type

Fast clamp sway brace attachment

Resources

Brochures

[Seismic engineering services](#)

[TOLCO seismic bracing overview brochure](#)

Catalogs

[Seismic engineering guidelines](#)

[Seismic bracing for mechanical, electrical, and plumbing systems catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - FIG 1000 2X1 1/4 FASTC EG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)