

Eaton FIG 120-4X12-PLN

Catalog Number: FIG 120-4X12-PLN

Eaton B-Line series TOLCO U-hanger, Steel, Plain, 4" pipe size, 560 lb design load, 1/2"X3" fastener size, 4"X12", U hanger

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series TOLCO U-hanger	FIG 120-4X12-PLN
UPC	Product Length/Depth
782051717648	0.375 in
Product Height	Product Width
12 in	4 in
Product Weight	Certifications
1.03 lb	UL/CUL listed

Application

Operating temperature - max

750 °F

Pipe size - max

4 in

Model

Size

1/2 inch x 3 inch fastener size

Type

U hanger

Load rating/capacity

Load capacity

560 lbs

Material/finish

Material

Steel

Resources

Catalogs

[pipe hangers](#)

Specifications and datasheets

[Eaton Specification Sheet - FIG 120-4X12-PLN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)