

# Eaton FIG 200-1-1{4}-PGL

Catalog Number: FIG 200-1-1/4-PGL

Eaton B-Line series TOLCO Trimline adjustable band hanger, 0.8710" H x 3.7910" L x 1.9510" W, Steel, Pre-galvanized, 650 temp, 1.25" pipe

## General specifications



Photo is representative

### Product Name

Eaton B-Line series TOLCO Trimline adjustable band hanger

### Catalog Number

FIG 200-1-1/4-PGL

### UPC

782051706659

### Product Length/Depth

3.791 in

### Product Height

0.871 in

### Product Width

1.951 in

### Product Weight

0.09 lb

### Certifications

cUL Listed

UL Listed



Powering Business Worldwide

## Application

### Application

Design permit hanger adjustment after installation

### Operating temperature - max

650 °F

### Pipe size - max

1.25 in

## Model

### Model

Trimline™ adjustable band hanger

### Type

Type 10

## Material/finish

### Finish

Pre-galvanized

### Material

Steel

## Resources

### Catalogs

[TOLCO fire protection solutions catalog](#)

[wall-studs-section-fastener-catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - FIG 200-1-1/4-PGL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)