

# Eaton FIG 200-2-PGL

Catalog Number: FIG 200-2-PGL

Eaton B-Line series TOLCO Trimline adjustable band hanger, 0.8710" H x 4.5410" L x 2.6630" W, Steel, Pre-galvanized, 650 temp, 2" pipe size

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series TOLCO Trimline adjustable band hanger	FIG 200-2-PGL
	<b>UPC</b>
	782051706758
<b>Product Length/Depth</b>	<b>Product Height</b>
4.541 in	0.871 in
<b>Product Width</b>	<b>Product Weight</b>
2.663 in	0.11 lb
<b>Certifications</b>	
cUL Listed	
UL Listed	

## Application

### Application

Design permit hanger adjustment after installation

### Operating temperature - max

650 °F

### Pipe size - max

2 in

## Model

### Model

Trimline™ adjustable band hanger

### Type

Type 10

## Material/finish

### Finish

Pre-galvanized

### Material

Steel

## Resources

### Catalogs

[wall-studs-section-fastener-catalog](#)

[TOLCO fire protection solutions catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - FIG 200-2-PGL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)