

Eaton FIG 200C-2-1{ }2-PVC

Catalog Number: FIG 200C-2-1/2-PVC

Eaton B-Line series TOLCO Trimline plastic coated adjustable band hanger, 0.9380"Hx5.2470"Lx3.08"W, Steel/plastic coated, 650 temp, 2.5"pipe

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series TOLCO Trimline plastic coated adjustable band hanger	FIG 200C-2-1/2-PVC
	UPC
	782051737257
Product Length/Depth	Product Height
5.247 in	0.938 in
Product Width	Product Weight
3.08 in	0.4 lb
Certifications	
cUL Listed	

Application

Application

Permits hanger adjustment after installation

Operating temperature - max

650 °F

Pipe size - max

2.5 in

Model

Model

"Trimline" adjustable band hanger

Type

Type 10

Material/finish

Material

Steel

Plastic coated

Resources

Catalogs

[TOLCO fire protection solutions catalog](#)

[wall-studs-section-fastener-catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - FIG 200C-2-1/2-PVC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)