

Eaton FIG 200F-2-1}2-PGL

Catalog Number: FIG 200F-2-1/2-PGL

Eaton B-Line series TOLCO Trimline felt lined adjustable band hanger, 0.9380"Hx5.2470"Lx3.08"W, Steel, Pre-galvanized, 650 temp, 2.5"pipe



Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series TOLCO Trimline felt lined adjustable band hanger	FIG 200F-2-1/2-PGL
	UPC
	782051706369
Product Length/Depth	Product Height
5.247 in	0.938 in
Product Width	Product Weight
3.08 in	0.2 lb
Certifications	
cUL Listed	

Application

Application

Design permit hanger adjustment after installation

Operating temperature - max

650 °F

Pipe size - max

2.5 in

Model

Model

TOLCO "Trimline" adjustable band hanger with felt lining

Special features

Protects CPVC plastic pipe from abrasion

Style

TOLCO

Type

Type 10

Material/finish

Finish

Pre-galvanized

Material

Steel

Resources

Catalogs

[wall-studs-section-fastener-catalog](#)

[TOLCO fire protection solutions catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - FIG 200F-2-1/2-PGL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia