

# Eaton FIG 200F-3{4}-PGL

Catalog Number: FIG 200F-3/4-PGL

Eaton B-Line series TOLCO Trimline felt lined adjustable band hanger, 0.8690"Hx3.1020"Lx1.3460"W, Steel, Pre-galvanized, 650 temp, 0.75"pipe



Photo is representative

## General specifications

### Product Name

Eaton B-Line series TOLCO Trimline felt lined adjustable band hanger

### Catalog Number

FIG 200F-3/4-PGL

### UPC

799038434412

### Product Length/Depth

3.102 in

### Product Height

0.869 in

### Product Width

1.346 in

### Product Weight

0.12 lb

### Certifications

cUL Listed



Powering Business Worldwide

## Application

### Application

Design permit hanger adjustment after installation

### Operating temperature - max

650 °F

### Pipe size - max

0.75 in

## Model

### Model

TOLCO "Trimline" adjustable band hanger with felt lining

### Special features

Protects CPVC plastic pipe from abrasion

### Style

TOLCO

### Type

Type 10

## Material/finish

### Finish

Pre-galvanized

### Material

Steel

## Resources

### Catalogs

[TOLCO fire protection solutions catalog](#)

[wall-studs-section-fastener-catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - FIG 200F-3/4-PGL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)