

# Eaton FIG 200H-2-1{2-3}8-PGL

Catalog Number: FIG 200H-2-1/2-3/8-PGL

Eaton B-Line series TOLCO heavy duty band hanger, 1.25" H x 4.8260" L x 3.2170" W, Steel, Pre-galvanized, 650 op temp, 2.5" max pipe size

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series TOLCO heavy duty band hanger	FIG 200H-2-1/2-3/8-PGL
	<b>UPC</b>
	782051706987
<b>Product Length/Depth</b>	<b>Product Height</b>
4.826 in	1.25 in
<b>Product Width</b>	<b>Product Weight</b>
3.217 in	0.56 lb
<b>Certifications</b>	
cUL Listed	
UL Listed	

## Application

### Application

Used extensively to support trapeze installations

### Operating temperature - max

650 °F

### Pipe size - max

2.5 in

## Model

### Model

Heavy duty band hanger

### Type

Type 10

## Material/finish

### Finish

Pre-galvanized

### Material

Steel

## Resources

### Catalogs

[TOLCO fire protection solutions catalog](#)

[wall-studs-section-fastener-catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - FIG 200H-2-1/2-3/8-PGL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)