

# Eaton FIG 4B 1 1/2 EG

Catalog Number: FIG 4B 1 1/2 EG

Eaton B-Line series TOLCO sway bracing pipe clamp, Electro-galvanized, 330 lbs, Steel, Fig 4B, 1.5" pipe size, Pipe clamp for sway bracing

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series TOLCO sway bracing pipe clamp	FIG 4B 1 1/2 EG
	UPC
	782051738100
<b>Product Length/Depth</b>	<b>Product Height</b>
0 in	3.43 in
<b>Product Width</b>	<b>Product Diameter</b>
0 in	1.5 in
<b>Product Weight</b>	<b>Certifications</b>
7.9 lb	OSHPD Certified

## Material type

### Finish

Electro-plated

### Material

Steel

## Product dimension

### Size

1.5 inch pipe size

## Other product information

### Model

Fig 4B

### Type

Pipe clamp for sway bracing

## Special features and ratings

### Load capacity

330 lbs

## Resources

### Brochures

[Seismic engineering services](#)

[TOLCO seismic bracing overview brochure](#)

### Catalogs

[Seismic bracing for mechanical, electrical, and plumbing systems catalog](#)

[Seismic engineering guidelines](#)

### Specifications and datasheets

[Eaton Specification Sheet - FIG 4B 1 1/2 EG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)