

# Eaton FS6-INTERNAL FAN

Catalog Number: FS6-INTERNAL FAN

Eaton H-Max Internal Fan, FR6, Variable frequency drives, Main fan, H-max, Main fan



Photo is representative

## General specifications

### Product Name

Eaton H-Max internal fan

### Catalog Number

FS6-INTERNAL FAN

### UPC

786685538952

### Product Length/Depth

6.25 in

### Product Height

2 in

### Product Width

4.5 in

### Product Weight

0.15 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

FS6 internal fan (IP54/NEMA 12)

Special features

Used with H-MAX Drives

NEMA rating

NEMA 12

Brochures

[Variable frequency drive - Product overview](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

Specifications and datasheets

[Eaton Specification Sheet - FS6-INTERNAL FAN](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)