

Eaton FSQC230

Catalog Number: FSQC230

Eaton Crouse-Hinds series Arktite FSQC interlocked receptacle with switch, 30A, Through feed, Two-wire, three-pole, Brass contacts, Copper-free aluminum, Spring door, 3/4"



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite FSQC FSQC230 interlocked receptacle with switch	UPC 782274416618
Product Length/Depth	Product Height
4.75 in	10 in
Product Width	Product Weight
5.75 in	11.7 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Amperage Rating

30A

Trade size

3/4"

Configuration

Two-wire, three-pole

Receptacle style

Spring door

Back box style

Through feed

Material

Copper-free aluminum

Contact material

Brass

Resources

3D models

[SP3D Design Package - Arktime FSQC Explosionproof Interlocked Receptacles](#)

Catalogs

[Arktime FSQC Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[Arktime FSQC Explosionproof Interlock Receptacles Canadian certification](#)

[Arktime FSQC Explosionproof Interlock Receptacles UL certification](#)

Installation instructions

[IF 1429A - FSQC - Replacing Collar Assembly](#)

[IF 748 - FSQ Receptacle Switch Replacement](#)

[IF 926 - FSQ Interlocked Receptacle and Switch](#)

[IF 83 - FSQ Interlocked Receptacle and Switch - Class I, Group B Hazardous \(Classified\) Locations](#)

[IF 1363 - FSQ 30 and 60 Amp Interlocked Receptacle and Switch](#)

Specifications and datasheets

[Eaton Specification Sheet - FSQC230](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)