

# Eaton FSQC3320

Catalog Number: FSQC3320

Eaton Crouse-Hinds series Arktite FSQC interlocked receptacle with switch, 30A, Through feed, Two-wire, three-pole, Brass contacts, Copper-free aluminum, Spring door, 1", Two-pole switch, 120-600 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite FSQC FSQC3320 interlocked receptacle with switch	UPC
	782274417394
Product Length/Depth	Product Height
4.75 in	10 in
Product Width	Product Weight
5.75 in	5.35 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Amperage Rating

30A

### Trade size

1"

### Configuration

Two-wire, three-pole

### Receptacle style

Spring door

### Back box style

Through feed

### Voltage rating

120-600 Vac

### Material

Copper-free aluminum

### Contact material

Brass

### Type

Two-pole switch

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds FSQC3320 3D drawing](#)

### 3D models

[SP3D Design Package - Arktime FSQC Explosionproof Interlocked Receptacles](#)

### Catalogs

[Arktime FSQC Explosionproof Interlock Receptacles catalog page](#)

### Certification reports

[Arktime FSQC Explosionproof Interlock Receptacles UL certification](#)

[Arktime FSQC Explosionproof Interlock Receptacles Canadian certification](#)

### Installation instructions

[IF 748 - FSQ Receptacle Switch Replacement](#)

[IF 1429A - FSQC - Replacing Collar Assembly](#)

[IF 83 - FSQ Interlocked Receptacle and Switch - Class I, Group B](#)

Hazardous (Classified) Locations

IF 926 - FSQ Interlocked Receptacle and Switch

IF 1363 - FSQ 30 and 60 Amp Interlocked Receptacle and Switch

Specifications and datasheets

Eaton Specification Sheet - FSQC3320



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)