

Eaton GHG2622601L0002

Catalog Number: GHG2622601L0002

Eaton Crouse-Hinds series GHG26 disconnect switch, 20A, Six-pole, With switch, 2 x 3/4" NPT entries, 12.2 HP/14.3 HP, Fiberglass-reinforced polyester, 1 NC contact configuration, #12 AWG auxiliary, #12 AWG terminals, 690 Vac/120 Vdc

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GHG26 disconnect switch	GHG2622601L0002
	EAN
	4250217420412
Product Length/Depth	Product Height
330 mm	175 mm
Product Width	Product Weight
140 mm	2.9 kg

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IECEX/ATEX

NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Enclosure type

With switch

Amperage Rating

20A

Configuration

Six-pole

Voltage rating

690 Vac/120 Vdc

Entry size

2 x 3/4" NPT

Horsepower

12.20 hp/14.30 hp

Material

Fiberglass-reinforced polyester

Special features

1 NC contact configuration, #12 AWG auxiliary, #12 AWG terminals

Resources

Brochures

[GHG26 Disconnect Switches flyer](#)

Catalogs

[GHG26 Series Explosion Protected Disconnect Switches catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG2622601L0002](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)