

Eaton GHG2650010L0003

Catalog Number: GHG2650010L0003

Eaton Crouse-Hinds series GHG26 disconnect switch, 125A, Three-pole, With switch, 2 x 1-1/2" NPT entries, 40 HP/75 HP, Fiberglass-reinforced polyester, 1 NO contact configuration, #12 AWG auxiliary, 2/0 AWG terminals, 690 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GHG26 disconnect switch	GHG2650010L0003
	EAN
	4251510767952
Product Length/Depth	Product Height
10.67 in	21.8 in
Product Width	Product Weight
10.83 in	35.2 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

IECEX/ATEX

NEC/CEC

NEC hazardous rating

Class II, Division 1

Class I, Zone 2

Class I, Division 2

Class II, Division 2

Class I, Zone 1

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Enclosure type

With switch

Amperage Rating

125A

Configuration

Three-pole

Voltage rating

690 Vac

Entry size

2 x 1-1/2" NPT

Horsepower

40 hp/75 hp

Material

Fiberglass-reinforced polyester

Special features

1 NO contact configuration, #12 AWG auxiliary, 2/0 AWG terminals

Resources

Brochures

[GHG26 Disconnect Switches flyer](#)

Catalogs

[GHG26 Series Explosion Protected Disconnect Switches catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG2650010L0003](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)