

Eaton GHG2732000L0005

Catalog Number: GHG2732000L0005

Eaton Crouse-Hinds series GHG273 light switch, 16A, Two-pole,
With switch, 1 x 1/2" NPT entry, Thermoplastic, 250 Vac

General specifications



Photo is representative

| Product Name | Catalog Number |
|---|-----------------|
| Eaton Crouse-Hinds series GHG273 light switch | GHG2732000L0005 |
| | EAN |
| | 4250217419966 |
| Product Length/Depth | Product Height |
| 120 mm | 75 mm |
| Product Width | Product Weight |
| 90 mm | 0.58 kg |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IECEX/ATEX

NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

Ingress protection (IP) ratings

IP66

Product specifications

Enclosure type

With switch

Configuration

Two-pole

Entry size

1 x 1/2" NPT

Voltage rating

250 Vac

Amperage Rating

16A

Material

Thermoplastic

Resources

Catalogs

[GHG273 Series Ex-Protected Light Switch catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG2732000L0005](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia