

# Eaton GHG5114306R3001

Catalog Number: GHG5114306R3001

Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle, 16A, Two-wire, three-pole, Nylon, M20, 220-240 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle	GHG5114306R3001
	EAN
	4250217426742
Product Length/Depth	Product Height
4.8 in	8.8 in
Product Width	Product Weight
3.5 in	2.3 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

IEC

### NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Amperage Rating

16 A

### Trade size

M20

### Configuration

Two-wire, three-pole

### Voltage rating

220-240 Vac

### Material

Nylon

## Resources

### Catalogs

[IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page](#)

### Specifications and datasheets

[Eaton Specification Sheet - GHG5114306R3001](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)