

Eaton GHG5117407L0001

Catalog Number: GHG5117407L0001

Eaton Crouse-Hinds series IEC 60309 hazardous area plug, 20A, Three-wire, four-pole, Nylon, 3/4", 3 phase 480 Vac

General specifications



Photo is representative

| | |
|---|-----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series IEC 60309 hazardous area plug | GHG5117407L0001 |
| | EAN |
| | 4250217437076 |
| Product Length/Depth | Product Height |
| 7.4 in | 3 in |
| Product Width | Product Weight |
| 3 in | 0.3 lb |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Amperage Rating

20A

Trade size

3/4"

Configuration

Three-wire, four-pole

Voltage rating

480 Vac

Material

Nylon

Resources

Catalogs

[IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG5117407L0001](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)