

# Eaton GHG5117407R0001

Catalog Number: GHG5117407R0001

Eaton's Crouse-Hinds series IEC 60309 hazardous area plug, 16A, Three-wire, four-pole, Nylon, M25, 500 Vac



Photo is representative

## General specifications

|   |                 |
|---|-----------------|
| Product Name  | Catalog Number  |
| Eaton Crouse-Hinds series IEC 60309 hazardous area plug | GHG5117407R0001 |
|   | EAN             |
|   | 4250217426902   |
| Product Length/Depth                                    | Product Height  |
| 7.4 in  | 3 in            |
| Product Width   | Product Weight  |
| 3 in  | 0.3 lb          |

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

IEC

### NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Amperage Rating

16 A

### Trade size

M25

### Configuration

Three-wire, four-pole

### Voltage rating

500 Vac

### Material

Nylon

## Resources

### Catalogs

[IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page](#)

### Specifications and datasheets

[Eaton Specification Sheet - GHG5117407R0001](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)