

# Eaton GHG5124506R3001

Catalog Number: GHG5124506R3001

Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle, 32A, Four-wire, five-pole, Nylon, M32, 380-415 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series IEC 60309 hazardous area interlock receptacle	GHG5124506R3001
	EAN
	4250217427152
Product Length/Depth	Product Height
4.7 in	11.5 in
Product Width	Product Weight
6.6 in	5.11 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

IEC

### NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Amperage Rating

32A

### Trade size

M32

### Configuration

Four-wire, five-pole

### Voltage rating

380-415 Vac

### Material

Nylon

## Resources

### Catalogs

[IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page](#)

### Specifications and datasheets

[Eaton Specification Sheet - GHG5124506R3001](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)