

Eaton GHG5147506R0001

Catalog Number: GHG5147506R0001

Eaton Crouse-Hinds series IEC 60309 hazardous area plug, 63A, Four-wire, five-pole, Nylon, M40, 380-415 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series IEC 60309 hazardous area plug	GHG5147506R0001
	EAN
	4250217427398
Product Length/Depth	Product Height
10.7 in	4.3 in
Product Width	Product Weight
4.3 in	2.6 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Amperage Rating

63A

Trade size

M40

Configuration

Four-wire, five-pole

Voltage rating

380-415 Vac

Material

Nylon

Resources

Catalogs

[IEC 60309 Hazardous Area Pin and Sleeve Devices catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG5147506R0001](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)