

Eaton GHG9601955R0003

Catalog Number: GHG9601955R0003

Eaton Crouse-Hinds series Ex-e cable gland, Non-armoured cable, Non-armoured gland, Polyamide 6, Increased safety, M20, Short thread



Photo is representative

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Ex-e cable gland | GHG9601955R0003 |
| | EAN |
| | 4250217429392 |
| Product Length/Depth | Product Height |
| 33 mm | 24 mm |
| Product Width | Product Weight |
| 24 mm | 0.01 kg |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

IECEX/ATEX

Ingress protection (IP) ratings

IP66

IP68

Product specifications

Protection type

Increased safety

Cable type

Non-armored

Non-armoured

Gland type

Non-armoured

Type

Short thread

Thread Size

M20

Thread type

Metric

Material

Polyamide 6

Resources

Catalogs

[Crouse-Hinds series CEAG GHG Non-metallic EX Cable Glands catalog page](#)

Certification reports

[Enlargement Gland IECEX Certificate of Conformity](#)

[Enlargement Gland Sizes M20 to M63 ATEX Certification](#)

[CEAG GHG Non-metallic Ex Cable Glands EU Type Examination Certificate](#)

Specifications and datasheets

[Eaton Specification Sheet - GHG9601955R0003](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)