

# Eaton GHQ2030

Catalog Number: GHQ2030

Eaton GHQ thermal magnetic circuit breaker, Circuit breaker, Fire alarm, red handle, 15 A, 14 kAIC, Single-pole, 277 V, Non-Interchangeable, GHP, GDB-Frame

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton GHQ thermal magnetic circuit breaker	GHQ2030
	UPC
	786689030537
<b>Product Length/Depth</b>	<b>Product Height</b>
1 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
1.3 in	0.85 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL 489

## Catalog Notes

Includes 4A33462H01 load clip.

## Physical Attributes

### Circuit breaker type

GHP

### Frame size

GDB

### Number of poles

Two-pole

### Type

Thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

14 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

277/480

## Miscellaneous

### Special features

Fire alarm, red handle

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - GHQ2030](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)