

Eaton GUA062 GB

Catalog Number: GUA062 GB

Eaton Crouse-Hinds series Condulet GUA sealing cover, 3" cover opening diameter, Feraloy iron alloy, Group B rated, 16 thread pitch

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA sealing cover	GUA062 GB UPC 782274196527
Product Length/Depth	Product Height
3.5 in	4 in
Product Width	Product Weight
2.53 in	0.6 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Cover opening diameter

3"

Thread pitch

16

Material

Feraloy iron alloy

Special features

Group B rated

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification \(Cover\)](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes Canadian certification \(Cover\)](#)

Installation instructions

[IF 1349 - GUA Sealing Covers](#)

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUA062 GB](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)