

Eaton GUA06 GB

Catalog Number: GUA06 GB

Eaton Crouse-Hinds series Condulet GUA surface cover, 3" cover opening diameter, Copper-free aluminum, Group B rated, 16 thread pitch

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA surface cover	GUA06 GB UPC 782274196510
Product Length/Depth	Product Height
3.5 in	3.5 in
Product Width	Product Weight
1.6 in	0.35 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Cover opening diameter

3"

Thread pitch

16

Material

Copper-free aluminum

Special features

Group B rated

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes Canadian certification \(Cover\)](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification \(Cover\)](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUA06 GB](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)