

# Eaton GUA0716

Catalog Number: GUA0716

Eaton Crouse-Hinds series Condulet GUA dome cover, 3-5/8" cover opening diameter, 4" exterior depth, Copper-free aluminum, 12 thread pitch



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet GUA dome cover	GUA0716
	<b>UPC</b>
	782274460109
<b>Product Length/Depth</b>	<b>Product Height</b>
5.75 in	4.5 in
<b>Product Width</b>	<b>Product Weight</b>
5 in	1.71 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

## Product specifications

### Cover opening diameter

3-5/8"

### Exterior depth

4"

### Thread pitch

12

### Material

Copper-free aluminum

## Resources

### Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

### Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes Canadian certification \(Cover\)](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification \(Cover\)](#)

### Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUA0716](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)