

Eaton GUA514

Catalog Number: GUA514

Eaton Crouse-Hinds series Condulet GUA dome cover, 5" cover opening diameter, 4" exterior depth, Copper-free aluminum, 12 thread pitch



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA dome cover	GUA514
	UPC 782274460901
Product Length/Depth	Product Height
6.06 in	5 in
Product Width	Product Weight
6.06 in	3.15 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Cover opening diameter

5"

Exterior depth

4"

Thread pitch

12

Material

Copper-free aluminum

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification \(Cover\)](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes Canadian certification \(Cover\)](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUA514](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)