

Eaton GUB6193 1 20

Catalog Number: GUB6193 1 20

Eaton Crouse-Hinds series GUB instrument housing, Top conduit opening, Feraloy iron alloy, 3/4", Housing with mounting plate for standard meters, Used with GUB06 basic housing, 7-11/16" maximum depth

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GUB instrument housing	GUB6193 1 20
	UPC
	782274085135
Product Length/Depth	Product Height
9.5 in	8.75 in
Product Width	Product Weight
7 in	43.43 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Type

Housing with mounting plate for standard meters

Used with

GUB06 basic housing

Trade size

3/4"

Conduit opening position

Top

Material

Feraloy iron alloy

Special features

7-11/16" maximum depth

Resources

Catalogs

[Crouse-Hinds series GUB Explosionproof Instrument Enclosures catalog page](#)

Certification reports

[GUB Explosionproof Instrument Enclosures UL certification](#)

Installation instructions

[IF 1112 - GUB Instrument Housings](#)

Specifications and datasheets

[Eaton Specification Sheet - GUB6193 1 20](#)