

# Eaton GUSC2052 AH

Catalog Number: GUSC2052 AH

Eaton Crouse-Hinds series GUSC snap switch, 20A/30A, Two-pole, With switch, 2 x 3/4" NPT entries, 2 HP, Feraloy iron alloy, Through feed, 3/4", 250/600 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GUSC snap switch	GUSC2052 AH
	UPC
	782274477701
Product Length/Depth	Product Height
6.06 in	6.19 in
Product Width	Product Weight
4.13 in	7.88 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Enclosure type

With switch

### Configuration

Two-pole

### Voltage rating

250/600 Vac

### Amperage Rating

20A/30A

### Horsepower

2 hp

### Trade size

3/4"

### Style

Through feed

### Entry size

2 x 3/4" NPT

### Material

Feraloy iron alloy

## Resources

### Catalogs

[GUSC Series Explosionproof Snap Switches catalog page](#)

### Certification reports

[GUSC Explosionproof Snap Switches UL certification](#)

### Installation instructions

[IF 1712 - GUSC Snap Switches](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUSC2052 AH](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)