

Eaton GUSC3120 40

Catalog Number: GUSC3120 40

Eaton Crouse-Hinds series GUSC circuit breaker load center, 40A, Feraloy iron alloy, 1 breaker, Two-pole, 1" trade size, 240 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GUSC circuit breaker load center	GUSC3120 40
	UPC
	782274004198
Product Length/Depth	Product Height
7.75 in	7.81 in
Product Width	Product Weight
5.81 in	10.22 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Number of breakers

1

Number Of Poles

Two-pole

Amperage Rating

40A

Trade size

1"

Material

Feraloy iron alloy

Voltage rating

240 Vac

Resources

Catalogs

[GUSC Series Explosionproof Circuit Breaker Load Centers catalog page](#)

Certification reports

[GUSC Explosionproof Circuit Breaker Load Centers UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - GUSC3120 40](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)