

# Eaton GUSC3210 40

Catalog Number: GUSC3210 40

Eaton Crouse-Hinds series GUSC circuit breaker load center, 40A, Feraloy iron alloy, 2 breakers, Single-pole, 1" trade size, 240 Vac

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series GUSC circuit breaker load center	GUSC3210 40
	UPC
	782274000015
Product Length/Depth	Product Height
7.75 in	7.81 in
Product Width	Product Weight
5.81 in	10.25 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Number of breakers

2

### Number Of Poles

Single-pole

### Amperage Rating

40A

### Trade size

1"

### Material

Feraloy iron alloy

### Voltage rating

240 Vac

## Resources

### Catalogs

[GUSC Series Explosionproof Circuit Breaker Load Centers catalog page](#)

### Certification reports

[GUSC Explosionproof Circuit Breaker Load Centers UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - GUSC3210 40](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)