

Eaton H1038DC

Catalog Number: H1038DC

Eaton Crouse-Hinds series throat bushing, Rigid/IMC, Insulated, Zinc die cast, 150°C, Threaded, 3"

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series throat bushing	H1038DC
	UPC
	662277003780
Product Length/Depth	Product Height
6.22 in	1.94 in
Product Width	Product Weight
3.43 in	0.33 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

Rigid/IMC

Insulator

Insulated

Thread

Threaded

Trade size

3"

Material

Zinc die cast

Temperature rating

150°C

Resources

Catalogs

[Crouse-Hinds series Insulating and Throat Bushings - Rigid-IMC catalog page](#)

Certification reports

[Insulating and Throat Bushings - Rigid-IMC Canadian certification](#)

[Insulating and Throat Bushings - Rigid-IMC UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - H1038DC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)