

Eaton H29R47F12CUNVLS52

Catalog Number: H29R47F12CUNVLS52

K-Factor Non Linear Transformer, Ventilated, K-4, Three-phase, PV: 208V, Taps: 1 at +5% FCAN, 2 at -5% FCBN, SV: 480Y/277V, 115°C, 112.5 kVA, Cu windings, Elec. Shield, Frame: 918AN



Photo is representative

General specifications

Product Name	Catalog Number
Eaton K-Factor nonlinear ventilated transformer	H29R47F12CUNVLS52
	UPC
	786680090776
Product Length/Depth	Product Height
30.68 in	62.18 in
Product Width	Product Weight
31.44 in	2243 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NEMA TP-1 efficient, Low Sound equal to 42 dB, Totally enclosed non-ventilated

Physical Attributes

Coil material

Copper

Design

K-4

Frame

918AN

Tap size

1 at +5% FCAN, 2 at -5% FCBN

Performance Ratings

Frequency rating

60 Hz

Volt ampere rating

112.5 kVA

Phase

Three-phase

Primary voltage

208 V

Secondary Voltage

480Y/277 V

Temperature rise

115 °C rise

Miscellaneous

Modification 1

Low sound 42 dB

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - H29R47F12CUNVLS52](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)