

Eaton H48M28F2216CU

Catalog Number: H48M28F2216CU

Eaton K-Factor nonlinear ventilated transformer, Copper windings, NEMA 2, FR945, 60 Hz, 220°C, 225 kVA, Floor, Three-phase, 480 Delta V, 208Y/120 Vac, NEMA ST-20, 115°C, 225 kVA, 480 Vac-208Y/120 Vac, WS62, 283B, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton K-Factor nonlinear ventilated transformer	H48M28F2216CU
	UPC
	786680192135
Product Length/Depth	Product Height
33.5 in	66.18 in
Product Width	Product Weight
42.18 in	1680 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Wiring connection

283B

Type

Energy-efficient ventilated transformer

Frame

FR945

Insulation

220 °C

Material

Copper windings

Mounting

Floor

Tap size

2 at +2.5%, 4 at -2.5%

Performance Ratings

Frequency rating

60 Hz

Kva Rating

225 kVA

Volt ampere rating

225 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Modification 1

Electrostatic shield

Special features

K-factor 4

Weathershield

WS62

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - H48M28F2216CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)