

Eaton H48M28F75NVLS47

Catalog Number: H48M28F75NVLS47

K-Factor Non Linear Transformer, Non-Ventilated, K-4, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 115°C, 75 kVA, Al windings, Elec. Shield, Frame: 916AN



Photo is representative

General specifications

Product Name	Catalog Number
Eaton K-Factor nonlinear ventilated transformer	H48M28F75NVLS47
	UPC
	786680055515
Product Length/Depth	Product Height
23.42 in	46.58 in
Product Width	Product Weight
28.22 in	983 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Totally enclosed non-ventilated, Low sound equal to 47 dB

Physical Attributes

Coil material

Aluminum

Design

K-4

Frame

916AN

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Performance Ratings

Frequency rating

60 Hz

Volt ampere rating

75 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Miscellaneous

Modification 1

Low sound 47 dB

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - H48M28F75NVLS47](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)