

Eaton H48M28T45CUNV

Catalog Number: H48M28T45CUNV

K-Factor Non Linear Transformer, Non-Ventilated, K-4, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 45 kVA, Cu windings, Elec. Shield, Frame: 916AN

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	H48M28T45CUNV
	UPC
	786680058790
Product Length/Depth	Product Height
23.42 in	48.56 in
Product Width	Product Weight
28.22 in	917 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Totally enclosed non-ventilated

Physical Attributes

Coil material

Copper

Design

K-4

Frame

916AN

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

150 °C rise

Volt ampere rating

45 kVA

Miscellaneous

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - H48M28T45CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)