

Eaton H48M47T75CUNV

Catalog Number: H48M47T75CUNV

K-Factor Non Linear Transformer, Non-Ventilated, K-4, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 480Y/277V, 150°C, 75 kVA, Cu windings, Elec. Shield, Frame: 916AN



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	H48M47T75CUNV
	UPC
	786680064869

Product Length/Depth	Product Height
23.42 in	46.58 in

Product Width	Product Weight
28.22 in	1237 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed	

from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Totally enclosed non-ventilated

Physical Attributes

Coil material

Copper

Design

K-4

Frame

916AN

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Non-ventilated transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

75 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

150 °C rise

Miscellaneous

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - H48M47T75CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)