

Eaton HCU2157D6N2

Catalog Number: HCU2157D6N2

Eaton Active Harmonic Correction unit, 157A, 7.2 kW watt loss, 600V rating, 50/60 Hz, Three-phase, Floor-mount, NEMA 2 enclosure



Photo is representative

General specifications

Product Name	Catalog Number
Eaton HCU2 active harmonic correction unit	HCU2157D6N2
	UPC 743172081995
Product Length/Depth 30.71 in	Product Height 87.32 in
Product Width 60.12 in	Product Weight 1636.6 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year IEC 61000 3-2 from the date of installation of the Product or eighteen (18) months from the IEEE Std. 519 date of shipment of the Product, whichever occurs first.	IEC 61000-3-4 UL 508C CSA Std. C22.2 No. 14

Product Category

Harmonic Correction Units

Special features

Integral disconnect

Amperage Rating

157A

Cable entry

Top or bottom

Enclosure

NEMA 2

Frequency rating

50/60 Hz

Mounting

Floor

Phase

Three-phase

Type

Active Harmonic Correction unit

Voltage rating

600 V

Watt losses

7.2 kW

Specifications and datasheets

Eaton Specification Sheet - HCU2157D6N2