

Eaton HEN10434LGRST

Catalog Number: HEN10434LGRST

Eaton B-Line series horizontal meter pack, Ringless, 3, ANSI 61 paint, Galvanized steel, Both, #6 AWG-350 KCMIL, #14 AWG-2/0 AWG, Side, 1, 3, 100 A, None,

General specifications



Photo is representative

Product Name

Eaton B-Line series horizontal meter pack

Catalog Number

HEN10434LGRST

UPC

782051408812

Product Length/Depth

5.25 in

Product Height

18.125 in

Product Width

37 in

Product Weight

42.059 lb

Certifications

UL

Electrical specifications

Amperage Rating

100 A

Material/finish

Material

Galvanized steel

Finish

ANSI 61 paint

Model

Number of wires

3

Bypass

None

Feed type

Both

Mounting method

Side

Number of poles

1

Line lug size

#6 AWG-350 KCMIL

Load lug size

#14 AWG-2/0 AWG

Cover/door type

Ringless

Standards

Degree of protection

3

Resources

Catalogs

[B line series metering](#)

Specifications and datasheets

[Eaton Specification Sheet - HEN10434LGRST](#)