

Eaton HGLL 5

Catalog Number: HGLL 5

Eaton Crouse-Hinds series HGLL grounding bushing, Rigid/IMC, Aluminum lug, #4-14 AWG, Malleable iron, 150°C, Threaded, 1-1/2"

General specifications



Photo is representative

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series HGLL grounding bushing | HGLL 5 |
| | UPC |
| | 784564113108 |
| Product Length/Depth | Product Height |
| 2.31 in | 0.81 in |
| Product Width | Product Weight |
| 2.31 in | 0.2 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

Rigid/IMC

Temperature rating

150°C

Lug material

Aluminum

Thread

Threaded

Trade size

1-1/2"

Lug size

#4-14 AWG

Material

Malleable iron

Resources

Catalogs

[Crouse-Hinds series Grounding Bushings - Rigid-IMC catalog page](#)

Certification reports

[Grounding Bushings - Rigid-IMC UL certification](#)

[Grounding Bushings - Rigid-IMC Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - HGLL 5](#)