

Eaton HGLL 6

Catalog Number: HGLL 6

Eaton Crouse-Hinds series HGLL grounding bushing, Rigid/IMC, Aluminum lug, #4-14 AWG, Malleable iron, 150°C, Threaded, 2"

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series HGLL grounding bushing	HGLL 6
	UPC
	784564113122
Product Length/Depth	Product Height
2.75 in	0.88 in
Product Width	Product Weight
2.75 in	0.27 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

Rigid/IMC

Temperature rating

150°C

Lug material

Aluminum

Thread

Threaded

Trade size

2"

Lug size

#4-14 AWG

Material

Malleable iron

Resources

Catalogs

[Crouse-Hinds series Grounding Bushings - Rigid-IMC catalog page](#)

Certification reports

[Grounding Bushings - Rigid-IMC UL certification](#)

[Grounding Bushings - Rigid-IMC Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - HGLL 6](#)